



FIDAS® FROG

MOBILE REAL-TIME AEROSOL SPECTROMETER

For Environment, Industry and Science

Made in Germany



Mobile Fine Dust Measurement With **FIDAS[®] FROG**

Whether it's fine dust pollution in the air, dust pollution at workplaces or measurements of the effectiveness of air filters: **FIDAS[®] FROG** covers a wide range of applications.

The mobile fine dust measuring device **FIDAS[®] FROG** works according to the proven principle of optical measurement and classification of individual particles. Palas has significantly advanced the development of this technology. In the **FIDAS[®] 200**, which is certified according to EN 16450, this principle has become a worldwide standard for the continuous monitoring of fine dust.

FIDAS[®] FROG is battery-powered, and thus very flexible and mobile, which makes it the perfect complement to the **FIDAS[®]** series. The detachable tablet connects to the measuring unit via Wi-Fi. It visualizes dust concentration trends and particle size distributions with high resolution. At the same time it is possible to change settings on the device, record measurement series and generate reports.

Application Examples



**MEASUREMENT OF PARTICULATE
MATTER IMMISSIONS AT ANY
LOCATION**



**WORKPLACE MEASUREMENTS
(EN 481)**



**STUDIES ON AEROSOL
DISPERSION INDOORS**



**MOBILE PARTICLE MEASUREMENT
ON THE FACTORY FLOOR**

Principle of Operation

Unlike photometers or nephelometers, the **FIDAS® FROG** uses the much more precise measuring principle of optical light scattering on the individual particle. This is ensured by a long-life, powerful LED light source and a highly sensitive photomultiplier. A notable advantage of the Palas measurement technology: Users can easily clean and calibrate the optical system on their own. Certified calibration dust for generating the test aerosol is included in the scope of delivery.



All measured values are visualized in real-time as a current value and by continuous graphic display on the user interface of **FIDAS® FROG**. Limit values for mass concentrations of the various PM fractions can be set individually. Limit exceedances are indicated immediately.

Special Advantages and Benefits

LATEST TECHNOLOGY

- Multifunctional tablet PC, connected to the measuring unit via Wi-Fi
- Integrated camera for documentation of the measurement task incl. report generation
- Time resolution 1 s, adjustable time averaging over longer periods of time
- Simple, proven and highly accurate on-site calibration of the optical sensor using supplied monodisperse test powder
- Option for an extended sample air inlet with sampling head for outdoor air measurements and for connection of an isokinetic sampling system

DIFFERENT MEASUREMENTS

- Particle measurement range from 180 nm to 93 μm , up to 100 mg/m^3 mass concentration or 20,000 particles/ cm^3 (single particle analysis)
- Continuous, simultaneous real-time measurement of multiple PM fractions
- Option to perform workplace measurements according to EN 481

EXTENSIVE OUTPUT OPTIONS

- Visualization of the measured data in real time and their course
- Data and parameters can be subsequently evaluated with Palas PDAnalyze software
- Real-time transmission of measured data

Technical Features

Measuring principle	Optical light scattering of single particles
Reported Data	PM ₁ , PM _{2.5} , PM ₄ , PM ₁₀ , TSP, C _N , particle size distribution T, rH, P
Measurement range (number C_N)	0–20,000 particles/cm ³
Measurement range (size)	0.18–93 µm
Measurement range (mass)	0–100 mg/m ³ (depending on the aerosol composition)
Size channels	32/decade, 256 raw data channels
Time resolution	1 s, moving average over longer periods configurable
Interfaces	USB-C, network connection via USB-Ethernet-adapter or Wi-Fi
Power supply	19–25 V (adapter supplied) or internal battery (running time approx. 8h)
Installation conditions	0–+40 °C
Dimensions (H • W • D)	100 • 240 • 150 mm
Weight	Approx. 2.1 kg

More Measurement Devices

... for real-time indoor air quality assessment.

To determine indoor infection risk, the AQ GUARD combines the best available particle measurement technology with precise measurement of CO₂ concentration in the air.



... for fine dust monitoring in real-time.

The measuring device AQ GUARD SMART is suitable as a supplement to official measurements, for monitoring and checking safe working conditions and for temporary fine dust measurement at various locations.



... for use in regulatory environmental measurement.

The aerosol spectrometer FIDAS[®] 200 continuously analyzes the fine dust particles present in the ambient air and, like the functionally identical variants FIDAS[®] 200 E and FIDAS[®] 200 S, is certified in accordance with the standards EN 16450, EN 15267-1 and -2.





As an aerosol technology expert, Palas® Germany is committed to providing users with solutions for the generation, conditioning, measurement and analysis of aerosol particles. Based on the unique advantages of its own technology, Palas® developed a variety of application cases in ambient air quality monitoring, particle filtration performance testing and various scientific research fields. Palas Instruments (Shanghai) Co., Ltd. is a wholly owned subsidiary of Hong Kong Palas (Asia) Limited. As one of the global branches of Palas GmbH, it has legally obtained the Palas trademark authorized by Palas GmbH in Exclusive use rights in China and Asia.

As a company that has passed the ISO 9001:2015 quality management system certification, Palas®'s test rig solutions can execute particle filtration performance tests for filter media and filter elements according to applicable international, national and regional standards. In terms of environmental protection, Palas®'s equipment meets the requirements of multiple environmental monitoring standards (EN 15267, EN 16450, HJ653, GBZ/T 192.6, etc.) for indoor and ambient PM2.5, PM10, particle number size distribution monitoring and analysis.

Palas (Asia) Limited, Hong Kong

Operational Office Address:

Palas Instruments (Shanghai) Co., Ltd.

5th Floor, Building 6C, No. 650 Shunqing Rd, Song Jiang District, 201612 Shanghai

Hotline: +86 400 784 6669

Email: info@palas.com.hk

Website: www.palas.com.hk