



Active control of the relative humidity from 10 to 80 % and temperature from -10 to 50 °C

Benefits

- Settable relative humidity: 10 – 80 %
- Temperature regulation of the air volume flow: 20 to 35 °C (-10 to 50 °C on request)
- Expansion of the inflow velocity to 4 cm/s – 2 m/s
- Integration of an U-SMPS into the MFP 3000 HF expands the size range for the measurement of filter efficiency at the MFP 3000 to 10 nm – 40 µm
- Quasi-simultaneous particle measurement in raw gas and pure gas
- Measurement of $C_{n,max} = 10^6$ particles/cm³ without dilution
- Internationally comparable measuring results, high distribution of the test system
- Top reproducibility of the test procedure
- Easy use of various test aerosols, such as SAE Fine and Coarse, NaCl/KCl, DEHS
- Top raw gas concentrations up to > 1000 mg/m³ ISO Fine or > 5000 mg/m³ ISO Coarse with fraction separation efficiency measurement for load testing
- Flexible filter test software FTControl
- Sequential programs for pressure loss measurement, fraction separation efficiency measurement and load measurement
- Easy to operate, fast induction even of untrained personnel
- Short set-up times
- Cleaning and calibration can be carried out by customers themselves

Applications

- Testing of filter media and of small filter elements in product development and during production monitoring with variable rel. humidity and temperature.
- Testing option based on ISO 11155-1 / DIN 71460-1 (cabin air filters), ISO 5011 (engine pre-air filters), ISO 16890 / EN779 / ASHRAE 52.2 (room air filters), EN 1822-3 (HEPA filters), CEN EN 143 and other standards in various versions.
- Simulation for testing
 - car interior air intake filters or engine air filters at high temperatures, under dusty and dry or extremely humid conditions
 - turbine air filters from power plants (like those exposed to salt particles at high humidity on the coast under bad weather condition)
 - performance of room air filters in summer (warm and humid / dry) and winter (cold / humid / dry)
 - performance of ice formation in the filter medium



<https://www.palas.de/product/mfp3000hf>

Datasheet

Parameter	Description
Measurement range (size)	0.2 – 40 µm (Promo® system), 5 – 1 µm (U-SMPS system)
Volume flow	1.2 – 72 m ³ /h (suction mode)
Power supply	400 V, 50 Hz
Dimensions	2,300 • 800 • 2,000 mm (H • W • D)
Temperature regulation	20 – 35 °C (-10 – 50 °C on request)
Luftfeuchteregelung	10 – 80 %
Inflow velocity	4 – 200 cm/s
Differential pressure measurement	0 – 20,000 Pa
Test area of the medium	100 cm ²
Aerosols	Dusts (e. g. SAE dusts), salts (e. g. NaCl, KCl), liquid aerosols (e. g. DEHS)
Aerosol concentrations	For SAE-Fine without additional dilution to 1,000 mg/m ³ (ISO A2 Fine)
Compressed air supply	6 – 8 bar

Palas GmbH
 Partikel- und Lasermesstechnik
 Greschbachstrasse 3 b
76229 Karlsruhe
 Germany

Managing Partner:
 Dr.-Ing. Maximilian Weiß
Commercial Register:
 register court: Mannheim
 company registration number: HRB 103813
 USt-Id: DE143585902



Contact: E-Mail: mail@palas.de Internet: www.palas.de Tel: +49 (0)721 96213-0 Fax: +49 (0)721 96213-33